

CAT. N° 0 405 86

**SOUNDER - IP21 - IK07 - 90 DB - 12/24/48 V= - WHITE**

Pack (number of units)	1
Volume (dm ³)	4,851
Weight (g)	460,00

Product characteristics**Sounders**

- Conform to EN 54-3 standard and CE CPR approved
- IP 21 - IK 07
- Flush-mounting in false ceiling
- Sound level: 90 dB at 2 meters - NF S 32-001 sound
- Voltage range: 10 - 58 V
- Average consumption: 12 V DC 5 mA
- 24 V DC 9 mA
- 48 V DC 13 mA

General characteristics

Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies

Documentation **Catalogue pages & additional information**

- [Description page \(p.697\)](#)

 **Agreements & certificates of conformity**

- [NFSSI Composant - DS 033 A2](#)

 **Installation instructions & related documents**

- [LE02620AC](#)

 **Environmental product profile**

- [Environnemental product sheet n°4 E0027B-FR](#)
- [Environnemental product sheet n°4 E0033A-FR](#)