

CAT. N° 0 405 91


SOUNDER BEACONS - IP65 - IK07 - 90 DB - 12/24/48 V= - RED

Pack (number of units)	1
Volume (dm ³)	1,135
Weight (g)	282,00

Product characteristics
Sounder beacons

- Conform to EN 54-3 standard and CE CPR approved
- Sound level: 90 dB at 2 meters - NF S 32-001 sound
- Red flash
- Voltage range: 10 - 58 V
- Average consumption: 12 V DC 23 mA ; 24 V DC 22 mA ; 48 V DC 23 mA
- IP 65 - IK 07
- Surface-mounting
- 2 cable glands supplied

General characteristics

Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies

Documentation

Catalogue pages & additional information

- [Description page \(p.697\)](#)


Environmental product profile

- [Environnemental product sheet n°4 E0074A-EN](#)


Installation instructions & related documents

- [LE02619AB](#)