

CAT. N° 5 552 58

**SURFACE MOUNTING SOCKET P17 - IP44 - 380/415 V~ - 32 A - 3P+E**

Pack (number of units)	10
Volume (dm ³)	36,628
Weight (g)	4 821,00

Product characteristics**Surface mounting sockets**

- Two possible angles (5° or 25°)

380/415 V~

- IP 44
- 32 A
- 3P+E

General characteristics

P 17 Tempra Pro IP 44 - LV 16 and 32 A - sockets, plugs, mobile sockets, appliance inlets and interlocked switched sockets

Documentation **Catalogue pages & additional information**

- [Selection chart \(p.380\)](#)
- [Description page \(p.382\)](#)
- [P 17 Tempra Pro](#)

 **Installation & technical data**

- [F01811EN-03](#)

 **Installation instructions & related documents**

- [LE05815AA-01](#)

 **Agreements & certificates of conformity**

- [CCC - CQC2016010203850868](#)
- [IMQ - CA02_05951](#)
- [OC / CB - FR 641754/A1](#)