

REF . 0 372 07


TERMINAL BLOCK VIKING 3 - SPRING - 2 CONNECT - 4 WIRES - PITCH 5 - BLUE


Emballage (nombre number of units)	60
Volume (dm ³)	1,93
Poids (g)	856,00

Caractéristiques du produit
Connecting

- Grey for standard circuit, blue for neutral conductor, orange for circuit not broken by the master isolating device

2 connections - 4 wires - 2 levels

- Colour : Blue
- Nominal cross-section : 4 mm²
- Capacity - Rigid wire : 0.5 to 6 mm²
- Capacity – Flexible wire : 0.5 to 4 mm²
- Flexible wire with ferrule : 0.5 to 2.5 mm²
- Pitch : 5 mm

Caractéristiques générales
Viking™ 3 terminal blocks with spring connection - for copper cables

- Screwless connection system, stainless steel spring type
- Used to make the electrical connection between 2 rigid copper wires, or flexible copper wires with or without ferrules
- Direct tool-free insertion of a rigid wire or flexible wire with ferrule, up to 6 mm pitch
- 2 areas for automatic insertion bridging combs (upper level only for 2-level blocks)
- For rails depth 15 mm, EN 60715 depth 7.5 mm and 15 mm

Documentation associée

Catalogue pages & additional information

- [Selection chart \(p.326-327\)](#)
- [Description page \(p.330\)](#)
- [Technical page \(p.336\)](#)
- [Viking™ 3 terminal blocks with spring connection](#)


Agreements & certificates of conformity

- UL recogn - 20100921-E60900
- IMQ - CA02.04199
- Ex - 002/E
- NF App Industri - NF208_1012
- VERITAS (BV) - 23393/BO BV
- ATEX - LCIE 16 ATEX 3049U - 02


Installation & technical data

- F01007EN-02