

CAT. N° 0 372 12



TERMINAL BLOCK VIKING 3 - SPRING - FOR CONDUCTOR - 1 CONNECT - 4 WIRES - PITCH 5

Pack (number of units)	40
Volume (dm ³)	1,256
Weight (g)	577,00

Product characteristics

For protection conductor

- Metal base
- Screwless fixing on rail
- PEN from 10 mm²

1 connection - 4 wires - 2 entries/2 outlets

- Colour : Green/yellow
- Nominal cross-section : 4 mm²
- Capacity - Rigid wire : 0.5 to 6 mm²
- Capacity – Flexible wire : 0.5 to 4 mm²
- Flexible wire with ferrule : 0.5 to 2.5 mm²
- Pitch : 5 mm

General characteristics

Viking™ 3 terminal blocks with spring connection - for copper cables

- Screwless connection system, stainless steel spring type
- Used to make the electrical connection between 2 rigid copper wires, or flexible copper wires with or without ferrules
- Direct tool-free insertion of a rigid wire or flexible wire with ferrule, up to 6 mm pitch
- 2 areas for automatic insertion bridging combs (upper level only for 2-level blocks)
- For rails depth 15 mm, EN 60715 depth 7.5 mm and 15 mm

Documentation



Catalogue pages & additional information

- [Selection chart \(p.326-327\)](#)
- [Description page \(p.330\)](#)
- [Technical page \(p.336\)](#)
- [Viking™ 3 terminal blocks with spring connection](#)



Agreements & certificates of conformity

- [NF App Industri - NF208_1009](#)
- [UL recogn - 20100921-E60900](#)
- [Ex - 002/F](#)
- [IMQ - CA02.04200](#)
- [VERITAS \(BV\) - 23393/BO BV](#)
- [ATEX - LCIE 16 ATEX 3049U - 02](#)



Installation & technical data

- [F01007EN-02](#)