

CAT. N° 7 646 87



## THERMOSTAT NILOÉ 230 V - IVORY

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,593
Weight (g)	100,00

## Product characteristics

**Electronic room thermostat**


- For direct radiant ceiling panels and underfloor heating
- Adjustment range: from 10 °C to 30 °C
- Frost protection 7 °C
- Adjustment precision: 0.5 °C
- 1 potential free N/O contact
- Switching capacity:
  - 8 A - 250 V~ - resistive circuit
  - 2 A - 250 V~ - inductive circuit
- Power supply: 230 V~ 50/60 Hz
- Adjustable brightness of LEDs
- Can be associated with a clock for comfort and eco mode
- Ivory

## General characteristics

**Niloé™ - shutter controls, keycard switches and thermostats**

- Mechanisms supplied with cover plates and support frames in flow-pack
- To be equipped with plates
- Screw terminals
- Fixing with screws or claws (supplied)

## Documentation

 **Catalogue pages & additional information**

- [Description page \(p.532\)](#)

 **Installation & technical data**

- [F02163EN/00](#)

 **Installation instructions & related documents**

- [LE09397AA](#)