

CAT. N° 0 280 57

**TRIP FREE SWITCH DMX<sup>3</sup>-I 1600 - FIXED VERSION - 4P - 1250 A**

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

**Product characteristics****Fixed version**

- Supplied with:
  - 4 auxiliary contacts: NO/NC
  - rear orientable terminals for horizontal and vertical connection with bars
  - door sealing
- Frame 1600
- 4P
- In : 1250 A

**General characteristics****Trip free switches DMX<sup>3</sup>-I 1600 - from 1000 to 1600 A**

- Conform to IEC 60947-3

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.157\)](#)
- [DMX3 1600 and DMX3-I 1600 - Frame 1600](#)
- [DMX3 1600 electronic protection units](#)

 **Installation & technical data**

- [F02194EN/04](#)
- [LE10707AA](#)

 **Installation instructions & related documents**

- [LE08437AC](#)