

CAT. N° 7 645 66



TV-R-SAT-SAT MULTIPLE STAR SOCKET NILOÉ - ATTENUATION 1.5 DB - WHITE

Pack (number of units)	10
Volume (dm ³)	3,762
Weight (g)	1 088,00

Product characteristics

Multiple TV star sockets

TV-R-SAT-SAT

- Low attenuation: 1.5 dB
- In 1: TV-R-SAT 1 / In 2: SAT 2
- White

General characteristics

Niloé™ - television star sockets

- Mechanisms supplied with cover plates and support frames. To be equipped with plates. Fixing with screws or claws (supplied)
- For DVBT, Cablecast and satellite installation. UHD TV compatible. Class A shielded star sockets LTE Ready (4G protected).
- Recommended coaxial cable: 17 VATC. Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch). Visual checking of the connection
- Meet EN 50083-4 and EN 50083-2 European directive. Low attenuation: less than 1 dB
- TV: male connector (Ø9.5 mm)
- R: female connector (Ø9.5 mm)
- SAT: "F type" connector
- TV: 5-68 / 120-862 MHz
- R: 87.5-108 MHz
- SAT: 950-2400 MHz

Documentation

Catalogue pages & additional information

- [Description page \(p.535\)](#)

Installation & technical data

- [S000093617EN-01](#)

Installation instructions & related documents

- [LE08365AA](#)