

CAT. N° 0 365 77

**VENTILATION GLAND - IP66 - IK08 - DRILLING \varnothing 40.5 MM**

Pack (number of units)	24
Volume (dm ³)	20,72
Weight (g)	3 008,00

Product characteristics**Natural ventilation****IP 66 - IK 08 ventilation glands for cabinets**

- Polyamide PA 6 - RAL 7035
- Drilling \varnothing 40.5 mm

General characteristics**Heat regulation for cabinets and enclosures - ventilators****Documentation****Catalogue pages & additional information**

- [Description page \(p.313\)](#)
- [Heat regulation for cabinets and enclosures](#)