

CAT. N° 0 775 98



## WIRELESS CHARGER + TYPE A USB MOSAIC - WHITE WITH METALLIC FINISHING PLATE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,516
Weight (g)	244,00

### Product characteristics

#### Wireless charger + Type-A USB - Mosaic version

- 1 A - 5 V/5 W charger with one 2.4 A/12 W USB port to power a second device
- Specially designed for work areas
- For installation in flush-mounting box, surface mounting box, workstation kit, column module, multioutlet extension for offices, etc
- To be fitted with a support and a plate depending on the selection of the wiring accessories ranges
- Comes with 2 induction antennae for fast intuitive smartphone charging.
- Recognition area: 50 x 80 mm
- Plate at an angle of 10° with non-slip coating to hold the terminal safely in place during charging
- Dimensions: 136.5 x 70 x 56.5 mm
- Anti-theft lock function
- Can be mounted in multiple horizontal positions
- White with metallic finishing plate
- 2 x 2.5 mm<sup>2</sup> terminals

### General characteristics

#### Mosaic™ Programme mechanisms - wireless power chargers

- Wireless power chargers for fast charging a smartphone with a Qi receiver
- Power supply standby mode consumption less than 0.07%
- Conform to the Qi WPC standard (Wireless Power Consortium): certified for professional Qi 1.2.3 projects
- Conform to EN 62479 standard (EMF emissions)
- Conform to ICNIRP specifications (health protection)
- Do not interfere with other wireless signals (Zigbee, TNT, GSM, 4G, etc)

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.886\)](#)



#### Installation & technical data

- [F02387EN-00](#)



#### Installation instructions & related documents

- [LE09620AB](#)