

CAT. N° 3 375 21



## XL<sup>3</sup> S 630 DISTRIBUTION ENCLOSURES WITH 16 MODULES WIDE - TOTAL 824X454X249 MM AND USABLE 750X350X249 MM

|                           |           |
|---------------------------|-----------|
| Pack (number of units)    | 1         |
| Volume (dm <sup>3</sup> ) | 103,275   |
| Weight (g)                | 18 120,00 |

### Product characteristics

#### Enclosures

##### 16 modules wide

- Faceplates: RAL 9003
- Body: RAL 7016
- Height total : 824 mm
- Height faceplate : 750 mm
- Width total : 454 mm
- Width usable : 350 mm
- Depth : 249 mm

### General characteristics

#### XL<sup>3</sup> S 630 - distribution enclosures

- Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately)
- Doors and side panels to be ordered separately
- Take protection devices up to 630 A
- Used to create assemblies certified IEC 61439-2
- IP 40 with door
- IP 30 without door
- Removable, separable top and bottom panels
- Can take Lina 25 ducting and IP 55 Cabstop cable gland plates

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.234\)](#)
- [Technical page \(p.254\)](#)

#### Installation & technical data

- [F02369EN-01](#)

#### Installation instructions & related documents

- [LE09457AE](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 17.083-R01](#)
- [LOVAG - IT 18.002](#)
- [LOVAG - IT 18.129](#)
- [LOVAG - IT 18.138](#)
- [LOVAG - IT 18.130](#)