

CAT. N° 3 375 72



XL³ S 630 DISTRIBUTION ENCLOSURES WITH 24 MODULES WIDE - TOTAL 1574X604X249 MM AND USABLE 1500X574X249 MM

| | |
|---------------------------|-----------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 259,2 |
| Weight (g) | 33 100,00 |

Product characteristics

Enclosures

24 modules wide

- Height total : 1574 mm
- Height faceplate : 1500 mm
- Width total : 604 mm
- Width usable : 574 mm
- Depth : 249 mm

General characteristics

XL³ S 630 - distribution enclosures

- Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately)
- Doors and side panels to be ordered separately
- Take protection devices up to 630 A
- Used to create assemblies certified IEC 61439-2
- IP 40 with door
- IP 30 without door
- Removable, separable top and bottom panels
- Can take Lina 25 ducting and IP 55 Cabstop cable gland plates

Documentation

Catalogue pages & additional information

- [Description page \(p.234\)](#)
- [Technical page \(p.254\)](#)

Installation & technical data

- [F02369EN-01](#)

Installation instructions & related documents

- [LE09457AE](#)

Agreements & certificates of conformity

- [LOVAG - IT 17.083-R01](#)
- [LOVAG - IT 18.002](#)
- [LOVAG - IT 18.129](#)
- [LOVAG - IT 18.138](#)
- [LOVAG - IT 18.130](#)