

CAT. N° 4 159 28

**DX<sup>3</sup> STOP ARC 6000 WITH BOTTOM SIDE SUPPLY - 1P+N  
ON RIGHT-HAND SIDE 230 V~ - 6A - 2 MODULES - C  
CURVE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,369
Weight (g)	207,00

**Product characteristics****Arc fault detection circuit breakers**

- Breaking capacity:
- 6000 - EN/IEC 60898 - 230/240 V~
- Compatible with prong-type supply busbars

**Single pole + neutral 230 V~**

- Neutral on right-hand side
- Nominal rating I<sub>n</sub> : 6 A
- Number of modules : 2

**General characteristics****DX<sup>3</sup> Stop Arc - bottom side supply - arc fault  
detection devices from 10 to 20 A**

- Conform to IEC/EN 62606
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries
- Specific use: fire prevention by arc detection

**Documentation****Catalogue pages & additional information**

- [Description page \(p.063\)](#)

**Installation & technical data**

- [F02541EN-02](#)