

CAT. N° 6 468 00

10" PDU LCS³ - 1 U - 4 X 2P+E - FRENCH STANDARD



Pack (number of units)	1
Volume (dm ³)	1,554
Weight (g)	492,00

Product characteristics

10" - PDU Basic

- 1 m power supply cord with French/German 2P+E plug

4 x 2P+E outlets

- French standard

General characteristics

Legrand cabling system LCS³ energy Distribution - horizontal (1U/2U) Basic Power Distribution Units (PDU)

- To provide ~ electric power for IT equipment in 19" enclosures
- 230 V - 50/60 Hz power supply
- 1U aluminium profile
- End cap with metallic brackets and cable holder shape
- Quick fixing (no screws) on 19" fixing centers. Can also be installed vertically by reverting the brackets (no screws)
- 2P+E outlets:
 - C13 and C19 standard outlets are equipped with cord locking system to avoid any accidental disconnection. Universal solution compatible with all the cords (C14 plugs for C13 and C20 plugs for C19)
 - French, German and British standard outlets are equipped with safety shutters
 - French and German standard outlets are inclined at 55°
- Black modules (outlets and functions)

Documentation



Catalogue pages & additional information

- [Selection chart \(p.725\)](#)
- [Description page \(p.771\)](#)
- [Technical page \(p.779\)](#)
- [Description page \(p.784\)](#)
- [Technical page \(p.790\)](#)
- [Technical page \(p.791\)](#)



Installation & technical data

- S000093176EN-07