

CAT. N° 4 460 83



## 19" CABLING CABINET LCS<sup>3</sup> - CAPACITY 37U - WIDTH 800 MM , DEPTH 1000 MM AND HEIGHT 1800 MM

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1824,768
Weight (g)	126 800,00

### Product characteristics

#### 19" cabling cabinets – 800 mm wide

- Suitable for use with patching, network and server equipment
- Stand-alone racks come with (removable) side panels
- Specifications:
  - frame: aluminium, demountable
  - supplied with a 25 mm or 100 mm plinth
  - load capacity: 1500 kg (static)
  - base size: 800 mm wide
- Doors (800 and 1000 mm racks):
  - (clear) glass front door, metal back door
  - right-hinged and fitted with a Fix-easy swivel handle with an EK-333 cylinder lock
- Roof: 3 or 4 cut-outs with 2 or 3 blind plates and 1 cable entry brush, depending on the frame size
- Interior: rack equipped with 4 x 19" profiles including height (U) indication. Distance to the rack front: set to 175 mm (pitch set to 740 mm). In case of racks depth 800 mm, distance to the back set to 87.5 mm (pitch set to 537.5 mm)
- Racks supplied with 20 cage nuts and screws
- Capacity: : 37 U
- Width: : 800 mm
- Depth: : 1000 mm
- Height: : 1800 mm

### General characteristics

#### Legrand cabling system LCS<sup>3</sup> Enclosures - cabling cabinets and accessories

### Documentation



#### Catalogue pages & additional information

- [Selection chart \(p.59\)](#)
- [Description page \(p.100\)](#)
- [Technical page \(p.111\)](#)



#### Installation & technical data

- [Datasheet LSC3 cabling cabinet](#)