

CAT. N° 0 506 63



2P+E MULTI-SOCKET PLUG - GERMAN STANDARD - 3 SIDE OUTLETS - TRANSPARENT - CARDBOARD

Pack (number of units)	10
Volume (dm ³)	6,64
Weight (g)	1 343,00

Product characteristics

2P+E multi-socket plugs - 16 A

- Max. admissible power 3.680 W at 230 V~

3 side outlets

- Cardboard
- Transparent

General characteristics

Multi-socket plugs and extensions - German standard

Documentation



Catalogue pages & additional information

- [Description page \(p.637\)](#)



Agreements & certificates of conformity

- [SNI - PCS.00174.01](#)
- [MEEI - UP 69260952 0001](#)
- [OC / CB - FR_704273](#)



Installation instructions & related documents

- [050663_LE02726AA](#)