

CAT. N° 7 532 10



2P+E/USB MIXED SOCKET VALENA IN'MATIC - GERMAN STANDARD - 16 A 250 V~ - IVORY

Pack (number of units)	1
Volume (dm ³)	0,887
Weight (g)	130,00

Product characteristics

German standard socket outlets 16 A - 250 V~

2P+E/USB mixed socket

- Supplied with cover plate
- Screw terminals
- To replace a traditional 2P+E socket without changing the wiring or the existing box
- To be installed in minimum 40 mm depth "regular" flush mounting box 2P+E 16 A + USB 1000 mA
- For a quick charging of tablets, smartphones, MP3 players, watches, etc
- Consumption in passive mode less than 0.1 W class II SELV
- Ivory Valena Life / Valena Allure (common Cat.No)

General characteristics

Valena™ IN'MATIC mechanisms - socket outlets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- IP 2X protection
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation

Catalogue pages & additional information

- [Description page \(p.502\)](#)

Agreements & certificates of conformity

- [OC / CB - HU-001826](#)
- [MEEI - UP 69253469 0001](#)

Installation & technical data

- [F01951EN-00](#)