

CAT. N° 0 778 41



## 2-WAY PUSH-BUTTON SOLIROC - 6 A 230 V~ - IP55 - NO-NC CONTACT

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,68
Weight (g)	177,00

### Product characteristics

#### Push-buttons 6 A - 230 V~ - IK 10 - IP 55

- Two-way push-button
- NO-NC contact

### General characteristics

#### Soliroc™ - control mechanisms IK 10

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.610\)](#)

#### Agreements & certificates of conformity

- [NF - NF012\\_1023](#)
- [QC / CB - FR\\_707077](#)

#### Installation & technical data

- [F00997EN-04](#)