

CAT. N° 8 330 09



## 3 POLE FAN SWITCH SYNERGY - 10 A 250 V~ - AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	154,00

### Product characteristics

#### 3 pole fan switches 10 A - 250 V~

- Conform to BS EN 60669-1: 2000
- With integrated padlockable safety block in OFF position
- Flush mounting back box: min. 25 mm deep
- Nominal plate dimensions: 86 x 86 mm
- Brushed stainless steel

### General characteristics

#### Synergy™ - fan switch and double pole switches - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.586\)](#)



#### Installation & technical data

- [F02319EN-00](#)