

CAT. N° 0 513 66

**3X2P+E EXTENSION - GERMAN STANDARD - IP44 WITH CAPS - RUBBER**

Pack (number of units)	5
Volume (dm <sup>3</sup> )	9,294
Weight (g)	1 500,00

**Product characteristics****German standard plugs 16 A - IK 08 and extensions**

- Screw terminals
- H07 RNF 3G 2.5 mm<sup>2</sup> max. cable
- Black

**Extensions**

- Bulk
- 3 x 2P+E outlets - IP 44

**General characteristics****Rubber single-socket plugs and extensions - German standard****Documentation****Catalogue pages & additional information**

- [Description page \(p.636\)](#)

**Agreements & certificates of conformity**

- [KSC - JW04005-16001](#)
- [OC / CB - FR 60055202C](#)
- [AENOR - 030/002195](#)