

CAT. N° 4 104 13



## ADD-ON MODULES DX<sup>3</sup> - 2P 230 V~ - 40 A - 300 MA - AC TYPE - FOR 1 MODULE DX<sup>3</sup> MCB

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,063
Weight (g)	210,00

### Product characteristics

2-pole - 230 V~

#### AC Type

- Sensitivity : 300 mA
- Nominal rating I<sub>n</sub> : 40 A
- Number of modules : 2

### General characteristics

#### Add-on modules DX<sup>3</sup> - for 1 module/pole DX<sup>3</sup> MCBs

- Conform to IEC 61009-1, IEC 62423 (F type)
- Voltage independent tripping except Cat.No 4 106 57/58/59
- AC type : detect AC components faults
- A type : detect AC and DC component faults
- F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping
- Detection of high frequency fault currents
- For mounting on the right-hand side of 1 module per pole DX<sup>3</sup> MCBs

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.070\)](#)
- [Technical page \(p.071\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

#### Installation & technical data

- F01305EN-05

#### Environmental product profile

- [Environnemental product sheet n°20 E0113A-FR](#)

#### Installation instructions & related documents

- [G8191D](#)

#### Agreements & certificates of conformity

- [NF - NF012\\_1340](#)
- [OC / CB - IT-11142](#)
- [CCC - 2016010307899559](#)