

CAT. N° 4 104 29



ADD-ON MODULES DX³ - 2P 230 V~ - 63 A - 30 MA - A TYPE - FOR 1 MODULE DX³ MCB

Pack (number of units)	1
Volume (dm ³)	1,063
Weight (g)	247,00

Product characteristics

2-pole - 230 V~

A Type

- Sensitivity : 30 mA
- Nominal rating I_n : 63 A
- Number of modules : 2

General characteristics

Add-on modules DX³ - for 1 module/pole DX³ MCBs

- Conform to IEC 61009-1, IEC 62423 (F type)
- Voltage independent tripping except Cat.No 4 106 57/58/59
- AC type : detect AC components faults
- A type : detect AC and DC component faults
- F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping
- Detection of high frequency fault currents
- For mounting on the right-hand side of 1 module per pole DX³ MCBs

Documentation



Catalogue pages & additional information

- [Description page \(p.070\)](#)
- [Technical page \(p.071\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)



Environmental product profile

- [Environmental product sheet n°20 E0113A-FR](#)



Agreements & certificates of conformity

- [NF - NF012_1340](#)
- [OC / CB - IT-11142](#)