

CAT. N° 4 104 71



ADD-ON MODULES DX³ - 3P 400 V~ - 40 A - 30 MA - AC TYPE - FOR 1 MODULE DX³ MCB

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 1,67 |
| Weight (g) | 281,00 |

Product characteristics

3-pole - 400 V~

AC Type

- Sensitivity : 30 mA
- Nominal rating I_n : 40 A
- Number of modules : 3

General characteristics

Add-on modules DX³ - for 1 module/pole DX³ MCBs

- Conform to IEC 61009-1, IEC 62423 (F type)
- Voltage independent tripping except Cat.No 4 106 57/58/59
- AC type : detect AC components faults
- A type : detect AC and DC component faults
- F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping
- Detection of high frequency fault currents
- For mounting on the right-hand side of 1 module per pole DX³ MCBs

Documentation

Catalogue pages & additional information

- [Description page \(p.070\)](#)
- [Technical page \(p.071\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Installation & technical data

- F01305EN-05

Environmental product profile

- [Environnemental product sheet n°20 E0113A-FR](#)

Installation instructions & related documents

- [G8191D](#)

Agreements & certificates of conformity

- [NF - NF012_1340](#)
- [OC / CB - IT-11142](#)
- [CCC - 2016010307899559](#)