

REF . 0 280 08

**AIR CIRCUIT BREAKER DMX<sup>3</sup> 1600 LCU 42 KA - FIXED VERSION - 4P - 1000 A**

Emballage (nombre number of units )	1
Volume (dm <sup>3</sup> )	107,653
Poids (g)	29 712,00

**Caractéristiques du produit****Fixed version**

- Supplied with
- 4 auxiliary contacts: NO/NC
- rear orientable terminals for horizontal and vertical connection with bars
- door sealing

**Breaking capacity Icu 42 kA (415 V~)**

- Frame 1600
- 4P
- In : 1000 A

**Caractéristiques générales****Air circuit breakers DMX<sup>3</sup> 1600 - from 630 to 1600 A**

- Automatic air circuit breakers must be equipped with DMX<sup>3</sup> 1600 electronic protection units Cat.No 0 281 64/65/66, imperatively ordered together for factory assembly
- Please ask for DMX<sup>3</sup> order form
- Conform to IEC 60947-2

**Documentation associée****Catalogue pages & additional information**

- [Description page \(p.156\)](#)
- [DMX3 1600 and DMX3-I 1600 - Frame 1600](#)
- [DMX3 1600 electronic protection units](#)

**Installation & technical data**

- [F02194EN/04](#)
- [LE10707AA](#)

**Installation instructions & related documents**

- [LE08437AC](#)