

CAT. N° 0 280 27



AIR CIRCUIT BREAKER DMX³ 1600 LCU 50 KA - FIXED VERSION - 3P - 1250 A

Pack (number of units)	1
Volume (dm ³)	91,091
Weight (g)	24 519,00

Product characteristics

Fixed version

- Supplied with
 - 4 auxiliary contacts: NO/NC
 - rear orientable terminals for horizontal and vertical connection with bars
 - door sealing

Breaking capacity Icu 50 kA (415 V~)

- Frame 1600
- 3P
- In : 1250 A

General characteristics

Air circuit breakers DMX³ 1600 - from 630 to 1600 A

- Automatic air circuit breakers must be equipped with DMX³ 1600 electronic protection units Cat.No 0 281 64/65/66, imperatively ordered together for factory assembly
- Please ask for DMX³ order form
- Conform to IEC 60947-2

Documentation

Catalogue pages & additional information

- [Description page \(p.156\)](#)
- [DMX3 1600 and DMX3-I 1600 - Frame 1600](#)
- [DMX3 1600 electronic protection units](#)

Installation & technical data

- [F02194EN/04](#)
- [LE10707AA](#)

Installation instructions & related documents

- [LE08437AC](#)