

CAT. N° 0 286 42



## AIR CIRCUIT BREAKER DMX<sup>3</sup> 2500 LCU 65 KA - FIXED VERSION - 3P - 1000 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	192,421
Weight (g)	55 400,00

### Product characteristics

#### Fixed version

- Supplied with
  - 4 auxiliary contacts: NO/NC
  - rear terminals for horizontal connection with bars
  - door sealing

#### DMX<sup>3</sup> - H 2500

- Breaking capacity Icu 65 kA (415 V~)
- Frame 2500
- 3P
- In : 1000 A

### General characteristics

#### Air circuit breakers DMX<sup>3</sup> 2500 and 4000 - from 800 to 4000 A

- Automatic air circuit breakers must be equipped with electronic protection unit, imperatively ordered together for factory assembly
- Please ask for DMX<sup>3</sup> order form
- Conform to IEC 60947-2

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.160\)](#)
- [DMX3 - frame 2500, 4000 & 6300](#)
- [DMX3 - electronic protection units](#)

#### Installation & technical data

- [Y2687H](#)
- [F01800EN/01](#)
- [Y2958H](#)

#### Installation instructions & related documents

- [Y2762C](#)