

CAT. N° 0 352 14



ATLANTIC STAINLESS STEEL CABINET 304L - VERTICAL VERSION WITH 1 METAL DOOR AND EXTERNAL DIMENSIONS 1200X800X300 MM

Pack (number of units)	1
Volume (dm ³)	389,367
Weight (g)	42 000,00

Product characteristics

Stainless steel cabinets 304L

- IP 66 according to standards
- IEC/EN 60529 (IP 55 for 2-door cabinets).
- IK 10 according to standards IEC/EN 62262 (EN 50102)
- Approvals: cULus: type 4x (type 12 for 2-door cabinets)
- Bureau Véritas, LCIE N° 80257-575296

Vertical version - 1 door

- Metal door
- External dimensions – Height : 1200 mm
- External dimensions – Width : 800 mm
- External dimensions – Depth : 300 mm
- Weight : 45 kg

General characteristics

Atlantic stainless steel cabinets - 304 L

- Suitable for harsh environments
- Brushed stainless steel finish
- Door with rounded vertical edges.
- Double bar lock.
- Upper and lower protective hoods
- Reversible cabinet
- Self-centering positioning system for the equipment
- Optional depth adjustment starting from 600 x 400 x 250 mm cabinets, with slide rails Cat.Nos 0 367 43/44/45
- Excellent resistance to corrosion and weather conditions
- Compatible with all Atlantic & Atlantic stainless steel accessories

Documentation

Catalogue pages & additional information

- [Selection chart \(p.288-289\)](#)
- [Description page \(p.293\)](#)

Installation & technical data

- [F00095EN--13](#)

Installation instructions & related documents

- [041169-06](#)

Agreements & certificates of conformity

- [VERITAS \(BV\) - 03212/I0 BV](#)
- [TUV GS - R60135228](#)
- [OC / CB - FR701269](#)
- [UL listed cULus - 20150526-E164087](#)