

CAT. N° 0 413 49


**BELL - FOR INDUSTRIAL AND ALARM USE - IP40 - IK08  
230 V~ - Ø100 MM GONG**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,932
Weight (g)	508,00

**Product characteristics**
**Class I**

- Double insulated
- Polyester corrosion resistant finish
- 200 hours maxi. continuous rating

**IP 40 - IK 08 - 50/60 Hz - Alternating current version**

- Ø 100 mm gong
- RAL 7037 Grey
- Voltage : 230 V~
- Consumption : 50 mA
- Average acoustic output at 1 m : 95 dB
- Weight : 0.8 kg

**General characteristics**
**Bells for industrial and alarm use**
**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.394\)](#)


**Environmental product profile**

- [Environnemental product sheet n°4 E0063A-EN](#)


**Installation instructions & related documents**

- [4065604/01](#)