

CAT. N° 0 920 64



BOX PLEKO - IP55 - IK07 - 220X170X86 - KNOCK-OUT ISO CABLE ENTRIES

Pack (number of units)	5
Volume (dm ³)	32,4
Weight (g)	2 613,00

Product characteristics

Rectangular boxes

- Grey RAL 7035

220 x 170 x 86 mm

- 12 knock-out entries for ISO 16/20
- 8 knock-out entries for ISO 20/25
- 4 knock-out entries for ISO 25/32

General characteristics

Plexo™ boxes IP 55 - IK 07 - with pre-cut knock-out ISO type cable entries

- Resistance to glow wire test: 750 °C (EN 60695 2-11)
- Operating temperature: - 25 °C to + 40 °C
- Knock-out entries
- Captive cover with clippable tie between box and cover except boxes 310 x 240 and 360 x 270
- Cover opens/closes with a 1/4 turn of a regular screwdriver, marking 0 and I
- Fixing with level adjustment :
 - At 2 or 4 internal points (screw Ø5 mm max.)
 - At the four corners out of wiring volume (screw Ø4 mm max.)
 - With brackets Cat.No 0 358 02
- Class II is ensured by protection caps (supplied) for the attachment screws

Documentation



Catalogue pages & additional information

- [Description page \(p.615\)](#)
- [Technical page \(p.616-617\)](#)