

CAT. N° 0 920 82



## BOX PLEKO - IP55 - IK07 - 310X240X124 - 24 ENTRY MEMBRANE GLANDS

Pack (number of units)	2
Volume (dm <sup>3</sup> )	37
Weight (g)	3 134,00

### Product characteristics

#### Rectangular boxes

- Grey RAL 7035

#### 310 x 240 x 124 mm

- 24 glands
- Ø cables and tubes accepted 4 to 40 mm

### General characteristics

#### Plexo™ boxes IP 55 - IK 07 - with direct entry membrane glands - 750 °C

- Resistance to glow wire test: 750 °C (EN 60695 2-11)
- Operating temperature: - 25 °C to + 40 °C
- Interchangeable membrane glands with direct entry
- Captive cover with clippable tie between box and cover except boxes 310 x 240 and 360 x 270
- Cover opens/closes with a 1/4 turn of a regular screwdriver, marking 0 and I
- Class II is ensured by protection caps (supplied) for the attachment screws
- Can be associated with Nylbloc auto terminal support Cat.No 0 343 98

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.614\)](#)
- [Technical page \(p.616-617\)](#)