

CAT. N° 6 170 57

**BRITISH STANDARD SOCKET OUTLET BELANKO WITH  
USB TYPE A CHARGER - 1 GANG UNSWITCHED - 13 A 250  
V~**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,426
Weight (g)	122,00

**Product characteristics****British Standard socket outlets - 13 A- 250 V~ with USB  
charger**

- Conform to BS 1363-2:2016
- Conform to IEC 60950-1

**1 gang**

- USB Type-A 2.4 A - 5 VDC - 12 W
- Consumption in passive mode less than 0.08 W
- 1 gang unswitched

**General characteristics****Belanko™ - socket outlets**

- Colour: White T084
- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

**Documentation****Catalogue pages & additional information**

- [Description page \(p.551\)](#)

**Agreements & certificates of conformity**

- [OC / CB - SE-86036](#)
- [OC / CB - SE-86036M1](#)

**Installation & technical data**

- [F02764EN-00](#)