

CAT. N° 8 330 88

**BRITISH STANDARD SYNERGY -1 GANG UNSWITCHED -15  
A 250 V~ -AUTHENTIC BRUSHED STAINLESS STEEL**

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

**Product characteristics****Socket outlets 15 A - 250 V~**

- Conform to BS 546
- Patented 3 pin safety shutter mechanism
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm

**1 gang unswitched**

- Brushed stainless steel

**General characteristics****Synergy™ - British standard socket outlets -  
Authentic**

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation****Catalogue pages & additional information**

- [Description page \(p.588\)](#)

**Installation & technical data**

- [F02265EN-00](#)