

CAT. N° 8 324 69

**BRITISH STANDARD SYNERGY -SINGLE POLE 1 GANG SWITCH -5 A -250 V~ SLEEK DESIGN GLOSSY GOLD**

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

**Product characteristics****Socket outlets 5 A - 250 V~**

- Conform to BS 546
- Patented 3 pin safety shutter mechanism
- For flush-mounting, back box to be min. 25 mm deep
- Nominal plate dimensions: 86 x 86 mm

**1 gang switched - single pole**

- Glossy gold

**General characteristics****Synergy™ - British standard socket outlets and USB sockets - Sleek Design**

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation****Catalogue pages & additional information**

- [Description page \(p.592\)](#)

**Installation & technical data**

- [F02276EN/00](#)