

CAT. N° 0 604 05

**BULKHEAD LIGHT - IP44 - IK06 - OVAL 60 W-E27 -PLASTIC GRID SCREW FIXING -GREY**

Pack (number of units)	12
Volume (dm ³)	27
Weight (g)	6 309,00

Product characteristics**Oval - IP 44 / IK 06**


- Polypropylene base
- Glass diffuser
- Galvanised steel or plastic
- Protection wire grid
- 3 side knockable entries, for Ø16, 20 mm - cable - 230 V - 50 Hz
- Self-extinguishing: 850 °C
- For compact fluorescent lamps
- Porcelain lampholder
- Screw terminals

12 W- E 27

- Grey
- Plastic grid - screw fixing

General characteristics

IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments

Documentation **Catalogue pages & additional information**

- [Description page \(p.677\)](#)
- [Weatherproof bulkhead lights](#)

 **Environmental product profile**

- [Environnemental product sheet n°A E5099A-EN](#)