

CAT. N° 0 624 02


BULKHEAD LIGHT PLE XO - IP54 - IK08 - RECTANGULAR - 75 W INCANDESCENT - RED

Pack (number of units)	5
Volume (dm ³)	29
Weight (g)	2 700,00

Product characteristics
IP 54 - IK 08 Plexo rectangular bulkhead lights – class II

- Polycarbonate diffuser, mounted on hinge
- Opening can be reversed Top/Base
- Supplied with one Plexo end cap, not assembled
- Through wiring or terminal connection (side or rear)
- Lampholder mounted on reflector (swivel pull-out type)
- Grey base self-extinguishing: 850 °C
- For E27 - 55 W halogen, 17 W compact fluorescent or 8 W LED lamps
- E 27
- With red diffuser

General characteristics
IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
Documentation
 **Catalogue pages & additional information**

- [Description page \(p.677\)](#)
- [Weatherproof bulkhead lights](#)

 **Agreements & certificates of conformity**

- [NF LUMINAIRES - NF105_1023](#)

 **Installation instructions & related documents**

- [0064AA9-08](#)

 **Environmental product profile**

- [Environnemental product sheet n°A E0083A-FR](#)