

CAT. N° 6 018 35


**CABINETS PLEKO<sup>3</sup> - IP65 - IK09 - 1 ROW - 18 MODULES**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	22,132
Weight (g)	2 684,00

**Product characteristics**
**Cabinets 18 modules per row**

- Number of rows : 1

**General characteristics**
**Plexo<sup>3</sup> - IP 65 weatherproof cabinets, multifunction sleeves and accessories**

- Self-extinguishing: resistance to incandescent wire 650°C.
- Allows to achieve assemblies conform to IEC 61 439 - 3
- Weatherproof cabinets - IP 65 - IK 09 - Class II
- Door and cabinet fully reversible. Removable chassis and faceplates from 2-row versions up
- 2-position rail for modular products and moulded cases. Spacing between rails 150 mm
- Can be fitted with perforated plates and solid faceplates for mounting non-modular products
- Lockable door handle, sealable cover and faceplate
- Shock-resistant polystyrene material
- Box colour light grey L750A, cover colour dark grey R746A
- Supplied without terminal blocks

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.286\)](#)
- [Technical page \(p.287\)](#)

 **Agreements & certificates of conformity**

- [QC / CB - 654748](#)

 **Installation & technical data**

- [F01043EN02](#)