

CAT. N° 0 362 05


**CABLE DUCTING LINA 25 - WIDTH 40 X HEIGHT 25 MM - BLUE 2525 - L. 2 M**

Pack (number of metres)	56
Volume (dm <sup>3</sup> )	53,434
Weight (g)	22 600,00

**Product characteristics**
**Lina 25 ducting**

- RAL 2525 blue PVC
- Conform to EN 50085-2-3
- 6.5 mm wide fingers with a 6 mm spacing
- Accepts up to 6 mm<sup>2</sup> without breaking side wall fingers
- Two pre-scored lines allow removal of fingers
- Bump on side wall fingers help cabling
- Rounded fingers prevent injury during cabling
- Conform to EN 50085 parts 2 and 3
- Plastic cable ducting (base + cover)
- Side perforations at intervals of 12.5 mm. Length: 2 m
- Width x height : 40 x 25 mm

**General characteristics**
**Lina 25™ cable ducting**
**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.348\)](#)
- [Technical page \(p.349\)](#)

 **Agreements & certificates of conformity**

- [NF 004 - 641237C](#)
- [UL recogn - E212478](#)
- [CSA - 700861](#)

 **Installation & technical data**

- [F01892EN-00](#)