

REF . 0 980 00

**CABLE GLAND PLASTIC - IP68 - ISO 12 - CLAMPING CAPACITY 3-6.5 MM - RAL 7001**

Emballage (nombre number of units )	25
Volume (dm <sup>3</sup> )	1,06
Poids (g)	174,00

**Caractéristiques du produit****Grey RAL 7001 cable glands**

- Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal and locking nut mounted

**ISO**

- Conform to EN 50 262
- ISO : 12
- Clamping capacity Ø Min. : 3 mm
- Clamping capacity Ø Max. : 6.5 mm

**Caractéristiques générales****Plastic cable glands IP 68 - ISO and PG****Documentation associée****Catalogue pages & additional information**

- [Description page \(p.316\)](#)