

REF . 0 980 22

**CABLE GLAND PLASTIC - IP68 - PG 11 - CLAMPING CAPACITY 5-10 MM - RAL 7001**

Emballage (nombre number of units)	25
Volume (dm ³)	1,06
Poids (g)	307,00

Caractéristiques du produit**Grey RAL 7001 cable glands**

- Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal and locking nut mounted

PG

- Conform to UTE C 68-300 and 68-311 guides recommendations
- PG : 11
- Clamping capacity Ø Min. : 5 mm
- Clamping capacity Ø Max. : 10 mm

Caractéristiques générales**Plastic cable glands IP 68 - ISO and PG****Documentation associée****Catalogue pages & additional information**

- [Description page \(p.316\)](#)