

CAT. N° 8 334 19



## CABLE OUTLET SYNERGY - 20 A 250 V~ - AUTHENTIC GLOSSY GOLD

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	126,00

### Product characteristics

#### Cable outlets

- Conform to BS 5733
- Fitted clamp and outlet membrane
- With terminal block
- Nominal plate dimensions: 86 x 86 mm

#### 20 A - 250 V~

- Glossy gold

### General characteristics

#### Synergy™ - shaver sockets, cable outlets, blanking plates and cord outlets - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.589\)](#)



#### Installation & technical data

- [F02358EN-00](#)