

CAT. N° 0 374 19

**COPPER BAR - FLAT RIGID - SECTION 32 X 5 MM - 400 TO 450 A - L. 1750 MM**

Pack (number of units)	4
Volume (dm <sup>3</sup> )	1
Weight (g)	9 300,00

**Product characteristics****Copper bars****Rigid, flat, threaded holes**

- Cross section : 32 x 5 mm
- I permissible IP ≤ 30 : 450 A
- I permissible IP > 30 : 400 A
- Holes Ø mm : M6
- Length : 1750 mm

**General characteristics****Copper bars and accessories**

- Standard distribution

**Documentation****Catalogue pages & additional information**

- [Selection chart \(p.260-261\)](#)
- [Description page \(p.260-261\)](#)
- [Selection chart \(p.282-283\)](#)
- [Description page \(p.282-283\)](#)