

CAT. N° 2 838 80

**DIMMER MALLIA - 60-500 W ROTARY CONTROL DIMMER - CHAMPAGNE**

Pack (number of units)	1
Volume (dm ³)	0,602
Weight (g)	131,00

Product characteristics**Leading edge dimmers**

- Conform to BS EN 60669-2-1

Rotary control dimmer

- 60-500 W for incandescent and halogen lamps 230 V~
- 60-500 VA ELV halogen lamps with ferromagnetic transformer and compensator Cat.No 0 401 39
- Champagne

General characteristics**Mallia™ - push-buttons, dimmers, automatic switches and other lighting functions - customisable colours**

- Painted polycarbonate front cover
- Compact mechanism for greater wiring space
- Supplied with 2 screws M 3.5 for BS boxes
- To be equipped with plates
- Dim.: 86 x 86 mm

Documentation**Catalogue pages & additional information**

- [Description page \(p.570\)](#)

**Agreements & certificates of conformity**

- OC / CB - SE-85252