

CAT. N° 0 126 25



DOMESTIC CARTRIDGE FUSE - CYLINDRICAL TYPE 10.3 X 31.5 - 25 A - WITHOUT INDICATOR

Pack (number of units)	10
Volume (dm ³)	0,045
Weight (g)	63,00

Product characteristics

Cylindrical

10.3 x 31.5

- Rating : 25 Amps
- Voltage ~ : 400 Volts
- Rupture capacity Copper : 20000 Amps
- Protected section : 4 mm²
- Color Indication : Blue

General characteristics

Domestic cartridge fuses

Documentation



Catalogue pages & additional information

- [Description page \(p.082\)](#)
- [Dimensions of din-rail equipment](#)



Agreements & certificates of conformity

- [NF - 656079/A1](#)