

CAT. N° 7 300 77



## DOUBLE POLE SOCKET OUTLET SYNERGY - SPECIAL E PIN - 2 GANG SWITCHED - 13 A - WHITE

Pack (number of units)	5
Volume (dm <sup>3</sup> )	2,955
Weight (g)	969,00

### Product characteristics

#### Socket outlets 13 A - 250 V~ - Special earth pin

- With safety shutter mechanism
- For flush-mounting, back box to be min. 25 mm deep

#### Double pole - switched

- 2 gang
- Nominal plate dimensions: 86 x 146 mm

### General characteristics

#### Synergy™ - British standard socket outlets - white

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.581\)](#)