

CAT. N° 8 334 12



## DOUBLE POLE SWITCH SYNERGY - BLUE LED POWER INDICATOR -20 A -250 V~ -AUTHENTIC GLOSSY GOLD

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	142,00

### Product characteristics

#### Double pole switches 20 A - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 25 mm deep
- Use cord outlet accessory Cat.No 7 300 53 for external cord outlet
- Nominal plate dimensions: 86 x 86 mm

#### DP switches + blue LED power indicator

- Glossy gold

### General characteristics

#### Synergy™ - fan switch and double pole switches - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.586\)](#)

#### Agreements & certificates of conformity

- [ASTA - 782](#)
- [QC / CB - FR\\_708093](#)

#### Installation & technical data

- [F02252EN-00](#)