

CAT. N° 0 415 33


ELECTROMECHANICAL SIREN - IP30 - IK05 - 24 V= - 12 W - 516 MA

Pack (number of units)	1
Volume (dm ³)	1,315
Weight (g)	241,00

Product characteristics
Electromechanical sirens IP 30 - IK 05

- Supplied with screws for semi-flush mounting

D.C. current

- Voltage : 24 V=
- Power : 12 W
- Consumption : 516 mA
- Average acoustic output at 1 m : 100 dB
- Weight : 0.2 kg
- Max. continuous rating : 200 hr

General characteristics
Electromechanical and electronic sirens
Documentation

Catalogue pages & additional information

- [Description page \(p.394\)](#)
- [Technical page \(p.395a\)](#)


Installation instructions & related documents

- [4065212/04](#)