

CAT. N° 0 660 04


EMERGENCY LIGHTING LUMINAIRE S8 - 8 WMAINTAINED - 3H - 110 LM

Pack (number of units)	1
Volume (dm ³)	3,007
Weight (g)	1 104,00

Product characteristics
8 W fluorescent non-maintained, maintained and combined units


- Certified to IEC 60598-2-22 and EN 60598-2-22 standards
- IP 42 - Class II
- Power supply: 230 V +/- 10% - 50/60 Hz
- Lamp and emergency operation test with a push-button
- Ni-Cd batteries
- Recharge time: 24 hours
- High capacity screw terminals: 2 x 2.5 mm²
- Charge monitor with a green LED

3 h duration - 110 lm

- Maintained - 110 lm - 3h (1 x 8 W)

General characteristics
S8 - indoor standard self-contained emergency lighting luminaires 8 W fluorescent - BS compliant

- Can be equipped with metallic protection grid Cat.No 0 626 91

Documentation
 **Catalogue pages & additional information**

- [Selection chart \(p.679\)](#)
- [Description page \(p.687\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)

 **Agreements & certificates of conformity**

- [OC / CB - ES1953-M3](#)

 **Installation instructions & related documents**

- [LE08468AA](#)