

REF . 0 660 00


EMERGENCY LIGHTING LUMINAIRE S8 - 8 WNON-MAINTAINED - 1H - 140 LM


Emballage (nombre number of units)	1
Volume (dm ³)	3,007
Poids (g)	914,00

Caractéristiques du produit
8 W fluorescent non-maintained, maintained and combined units


- Certified to IEC 60598-2-22 and EN 60598-2-22 standards
- IP 42 - Class II
- Power supply: 230 V +/- 10% - 50/60 Hz
- Lamp and emergency operation test with a push-button
- Ni-Cd batteries
- Recharge time: 24 hours
- High capacity screw terminals: 2 x 2.5 mm²
- Charge monitor with a green LED

1 h duration - 140 lm

- Non-maintained - 140 lm - 1h (1 x 8 W)

Caractéristiques générales
S8 - indoor standard self-contained emergency lighting luminaires 8 W fluorescent - BS compliant

- Can be equipped with metallic protection grid Cat.No 0 626 91

Documentation associée
 **Catalogue pages & additional information**

- [Selection chart \(p.679\)](#)
- [Description page \(p.687\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)

 **Agreements & certificates of conformity**

- [OC / CB - ES1953-M3](#)

 **Installation instructions & related documents**

- [LE08468AA](#)