

CAT. N° 7 521 65



ENERGY SAVING SWITCH VALENA LIFE - 10 AX 250 V~ - WITH COVER PLATE - WHITE

Pack (number of units)	1
Volume (dm ³)	0,824
Weight (g)	133,00

Product characteristics

Switches 10 AX - 250 V~

Energy saving switches

- Automatic terminals
- Installed and works like a conventional switch/2-way switch
- But in addition, it switches off automatically after 10 minutes if no movement is detected by the built-in IR detector cell
- Detection field 120°. Detection range 8 m
- Compatible with any lamp:
 - 12-150 W: incandescent and 230 V halogen
 - 12-150 VA: lamps with ferromagnetic or electronic ballast
 - 8-30 W (or 650 mA): LED and CFL
- All types of lamp can be mixed on the same circuit
- Ideal for rooms where the light may be left switched on needlessly (child's bedroom, box room)
- White

General characteristics

Valena™ Life - switches with cover plate

- Valena In'Matic mechanisms supplied with cover plates and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- After clipping in the rocker, all LED lamps light up blue
- Flowpack packaging: robust protection to ensure optimum operation

Documentation

Catalogue pages & additional information

- [Description page \(p.516\)](#)

Installation & technical data

- [F01984EN-02](#)

Installation instructions & related documents

- [LE07457AB](#)