

CAT. N° 0 427 86


**EQUIPMENT TRANSFORMER 1 PHASE - PRIM 230-400 V /  
SEC 115-230 V - 63 VA**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	3,821
Weight (g)	1 359,00

**Product characteristics**
**Circuits isolation**
**Input voltage = 230-400 V~ Output voltage = 115-230 V~**

- Power : 63 VA
- Primary terminal flexible cable : 1 to 4 mm<sup>2</sup>
- Secondary terminal flexible cable : 1 to 4 mm<sup>2</sup>

**General characteristics**
**Equipment transformers - single-phase**

- IP 2X or XXB up to 450 VA - up to 310 VA in 12-24 V - (coupling strip not mounted) - IK 04
- Clip on fixing possibility up to 160 VA with accessories Cat.No 0 044 16 or 0 428 99
- Transformers with 2 secondary voltage supplied with coupling strip
- Transformers up to 450 VA supplied with isolated strip for 0 V connection secondary / earth (except Cat.No 0 428 46)
- Conform to IEC EN 61558-2-6 for 12 V, 24 V and 48 V and conform to IEC EN 61558-2-4 for 115 V and 230 V
- Products suitable for building equipment conforming to standards EN 61131-2, EN 60204-1 and EN 61 439-1

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.361\)](#)
- [Technical page \(p.365\)](#)
- [Technical page \(p.367\)](#)
- [Protection of transformers and their lines](#)